



Product Name	Full Automatic Tablet Packing Machine
Model	Xana-U4002
Number of Rotary Cassettes	400
Footprint	W1160 mm × D886 mm × H1982 mm
Weight	885kg (Without Rotary Cassettes)
Power Source	220 - 240VAC / 100 - 120VAC, Single phase
	3.5A (230VAC)
Frequency	50Hz / 60Hz
Noise Level	Under 70dB
Power Consumption	Standby state: 250W
	Max state: 650W or less
Pouch Size	W80 mm x H70 mm
Packing Speed	52 pouches per minute
Applicable Standard	EMC: 2004/108/EC
	LVD: 2006/95/EC
	R&TTE: 1999/5/EC
	RoHS: 2011/65/EU





# Tosho Xana series Accurate and high speed, reliable Full Automated Tablet Packing Machine

Xana-U4002 provides compliance packaging and increases productivity. This is Tosho Xana generation product with years of experience in pharmacy automation, enhancing the safety and performance.

# Safety

### ■ Rotary Cassettes Automatic Identification

Each rotary cassette is identified automatically by Intelligent Feeder. It ensures the correct cassettes are being employed. LED flashes and gives notice if the cassette is being employed improperly. If the routine dispensing is started by unnoticed, the Intelligent Feeder base locks the cassette which placed in the wrong position so the tablets would not be dispensed by error.



### ■66 cells Conveyor Unit with LED Guide

66 cells Conveyor Unit holds tablets filled manually. Each cell has LED guides and it indicates the correct position to fill the tablet. This allows easy and safely filling of multiple medications.



## Printing

### **■**Custom Layout

- · Standard fonts of Windows OS
- · Images including pictures, logos, barcodes (Code 39 and 128) QR codes, special characters, can be customized and printed as you wish.
- Print layout can be easily changed and stored multiple layouts by simple operation.



### ■Print Quality

- · Clear and legible printing is easy to understand when patients should be taking their medication.
- · Not water soluble and easily rub, wash or wear off of printing information.

\* Microsoft, Encarta, MSN, and Windows, of the United States Microsoft Corporation, are registered trademarks or trademarks in the United States and other countries









High Speed and Accuracy

Xana-U4002' s dispensing speed is 52 pouches per minute. High speed and accurate, continued dispensing improves its production efficiency.

### All U2 Function

All U2 is available with Xana-U4002 and this function increases efficiency. Each cassette can be placed freely and interchangeable in the drawers. Automatically identified each time the cassettes are placed in the drawers.



# Operability

### ■ Dose Dispensing Control System FILIA

FILIA is a control system for Full Automatic Tablet Packing Machine and allows you easy and efficient management of the machine and related dispensing data. FILIA can be interfaced with your current software system.

### Packing Unit

Packing unit is designed to easily clean and replacing packing paper and ink-ribbon.



### ■ Alarm Light

Alarm light indicates machine state visually. Easy to check the machine conditions.



### ■Slide Cabinet

Four of drawer-type slide cabinets hold 400 rotary cassettes. Each cabinet can be locked to ensure its security.

